

# ACCU-CAL™ 50-LED Radiometer

Consistent light curing requires periodic monitoring of light energy intensity and dosage levels. The ACCU-CAL™ 50-LED radiometer is simple to operate and offers accurate measurement of curing energy. The ACCU-CAL™ 50-LED can measure energy levels emitted from lightguides (3 mm, 5 mm, and 8 mm), BlueWave® QX4™ LED wands, and LED flood lamps. A spectral sensitivity range of 350 - 450 nm and intensity measurement from 1 mW/cm<sup>2</sup> to 40 W/cm<sup>2</sup>, makes this unit ideal for measuring LED curing source energy levels. A specially designed photo-sensor assembly provides repeatable measurements and protection from high temperatures associated with some LED systems on the market.

**Simple to Operate ■ Set Screw Locks Lightguide in Place ■ PTB and NIST Traceable**



ACCU-CAL™ 50-LED for measuring flood lamps only. PN **40519**



ACCU-CAL™ 50-LED for measuring LED spot lamps and flood lamps. PN **40505**

## Three Reasons to Use a Radiometer

- **Maintaining a Reliable Light-Curing Process** – A radiometer helps to ensure that a light-curing system is providing the intensity and dosage levels required for successful curing.
- **Providing a Worker-Friendly Light-Curing Process** – The ACCU-CAL™ 50-LED is sufficiently sensitive to measure the intensity of stray or reflected energy (as little as 1 mW/cm<sup>2</sup>). Dymax recommends that worker UVA exposure not exceed 1 mW/cm<sup>2</sup>. For reference, UV (320-395 nm) intensity on a sunny day can range from 2-6 mW/cm<sup>2</sup>.
- **Measuring Transmission Rates Through Substrates** – A radiometer can be used to measure the transmission rates of various wavelengths through substrates that sometimes absorb various frequencies of energy. To assure an effective curing process it is critical to measure the light intensity reaching the cure site below any intervening substrate.

SPECIFICATIONS	
Spectral Sensitivity	350 to 450 nm
Intensity Range	1 mW/cm <sup>2</sup> to 40 W/cm <sup>2</sup>
Resolution	Intensity (1 mW/cm <sup>2</sup> ; to three significant digits) Dose (1 mJ/cm <sup>2</sup> )
Calibration Period	12 months
Operating Temperature Ranges	Optometer: +5 to +40°C Detector: 120°C continuous, Peak 200°C
Measurement Modes	Intensity (mW/cm <sup>2</sup> ) Peak Intensity (mW/cm <sup>2</sup> ) Dose (m J/cm <sup>2</sup> )
Light Sources	Lightguides (3 mm, 5 mm, and 8 mm), BlueWave® QX4™ LED Wands, LED Flood Lamps
Power Supply	Two (2) AA batteries
Battery Life	250 hours (automatic shutoff after 1 hour)
Sensor Dimensions	Photo-Sensor Diameter = 9 mm Diameter = 37 mm Thickness = 8 mm Cable Length = 1 M
Meter Dimensions	145 mm (Length) x 63 mm (Width) x 30 mm (Thickness)

RADIOMETERS and ACCESSORIES		
Product	Part #	Description
ACCU-CAL™ 50-LED for LED Spot and Flood Units	40505	Complete radiometer with 3 mm, 5 mm, and 8 mm lightguide adapters, lightguide simulator*, and an optical adapter for use with the BlueWave® QX4™; includes storage/carrying case
ACCU-CAL™ 50-LED for LED Flood Units	40519	Complete radiometer for LED flood and conveyor systems; includes storage/carrying case
Flood to Spot Adapter Kit	39554	Kit includes three lightguide adapters (3 mm, 5 mm, and 8 mm) and a lightguide simulator*
3 mm Lightguide Adapter	39556	Fits 3 mm ID lightguides (5 mm OD)
5 mm Lightguide Adapter	39557	Fits 5 mm ID lightguides (7 mm OD)
8 mm Lightguide Adapter	39558	Fits 8 mm ID lightguides (10 mm OD)
Lightguide Simulator	38408	Lightguide simulator (Fits all standard lightguide entrance fittings)
BlueWave® QX4™ Optic Adapter Upgrade Kit	42218	This option is for customers who already own an ACCU-CAL™ 50-LED. The kit includes the optic adapter and updated software and calibration for your existing radiometer. The customer's radiometer must be returned to Dymax for programming and calibration.

\*A lightguide simulator is used to measure direct spot lamp intensity (required to calculate lightguide transmission)

### RADIOMETER CALIBRATION

Dymax recommends recalibrating the ACCU-CAL™ 50-LED radiometer annually to ensure proper operation of the instrument. Calibration services are available through Dymax. Please contact Dymax Customer Support for more information.



© 2009-2015 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by Dymax Corporation, U.S.A.

Please note that most curing system applications are unique. Dymax does not warrant the fitness of the product for the intended application. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dymax standard Conditions of Sale published on our website. Dymax recommends that any intended application be evaluated and tested by the user to ensure that desired performance criteria are satisfied. Dymax is willing to assist users in their performance testing and evaluation by offering equipment trial rental and leasing programs to assist in such testing and evaluations.

LI276DA 11/23/2015

Dymax Corporation  
860.482.1010 | info@dymax.com | [www.dymax.com](http://www.dymax.com)

Dymax Europe GmbH  
+49 (0) 611.962.7900 | info\_de@dymax.com | [www.dymax.de](http://www.dymax.de)

Dymax Engineering Adhesives Ireland Ltd.  
+353.1.231.4696 | info\_ie@dymax.com | [www.dymax.ie](http://www.dymax.ie)

Dymax Oligomers & Coatings  
860.626.7006 | info\_oc@dymax.com | [www.dymax-oc.com](http://www.dymax-oc.com)

Dymax UV Adhesives & Equipment (Shanghai) Co. Ltd.  
+86.21.37285759 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

Dymax UV Adhesives & Equipment (Shenzhen) Co. Ltd.  
+86.755.83485759 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

Dymax Asia (H.K.) Limited  
+852.2460.7038 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

Dymax Asia Pacific Pte. Ltd.  
+65.6752.2887 | info\_ap@dymax.com | [www.dymax-ap.com](http://www.dymax-ap.com)

Dymax Korea LLC  
+82.2.784.3434 | info\_kr@dymax.com | [www.dymax.com/kr](http://www.dymax.com/kr)